

Wireless MIDI Configuration for ONSONG (Master), Voicelive 3 (Slave) and BeatBuddy (Slave)

SETUP

ONSONG
Utilities:

-Editors:

-MIDI:

-Wrench icon:

-MIDI Enabled: ON

-One-based Index (1-128): OFF
(in order to match associated tables I
created for the BB and VL3)

Main Pedal:

-MIDI Settings:

-MIDI In:

-System Real Time:

-Sync: Enable

-MIDI Channel Number: Ch. 1

-MIDI Out:

-Output Type: MIDI-Merge

-Output Channel: Ch. 2

Setup:

-MIDI:


-Input Source: MIDI PORTS

-Input Channel Number: 2


-MIDI TEMPO: ON (if you want the
VL3 to Sync tempo, as slave, with
the BB)

ONSONG: Program Change MIDI instructions

Press & hold
song name




Press the + sign
to add MIDI
instructions



Type Channel,
*Program, *MSB, *LSB
(*see tables), then
"Done"

Select (Ej.):
BB: Channel1
VL3: Channel 2



BEATBUDDY MIDI-PATCH TABLE

LSB = BB FOLDER# – 1										
PROGRAM = BEAT# – 1 (Max. 99 Songs/Folder)										
BB		MIDI				BB		MIDI		
FOLDER#	SONG#	PROGRAM	MSB	LSB		FOLDER#	SONG#	PROGRAM	MSB	LSB
1	1	0	0	0		3	1	0	0	2
	2	1	0	0			2	1	0	2
	3	2	0	0			3	2	0	2
	4	3	0	0			4	3	0	2
	5	4	0	0			5	4	0	2
	6	5	0	0			6	5	0	2
	7	6	0	0			7	6	0	2
	8	7	0	0			8	7	0	2
	9	8	0	0			9	8	0	2
	10	9	0	0			10	9	0	2
										
	99	98	0	0			99	98	0	2
2	1	0	0	1		4	1	0	0	3
	2	1	0	1			2	1	0	3
	3	2	0	1			3	2	0	3
	4	3	0	1			4	3	0	3
	5	4	0	1			5	4	0	3
	6	5	0	1			6	5	0	3
	7	6	0	1			7	6	0	3
	8	7	0	1			8	7	0	3
	9	8	0	1			9	8	0	3
	10	9	0	1			10	9	0	3
										
	99	98	0	1			99	98	0	3

AND SO ON...

VOICELIVE 3 MIDI-PATCH TABLE

PRESET	1-128			PRESET	129-256			PRESET	257-384			PRESET	385-500		
	PROGRAM	MSB	LSB		PROGRAM	MSB	LSB		PROGRAM	MSB	LSB		PROGRAM	MSB	LSB
1	0	0	0	129	0	0	1	257	0	0	2	385	0	0	3
2	1	0	0	130	1	0	1	258	1	0	2	386	1	0	3
3	2	0	0	131	2	0	1	259	2	0	2	387	2	0	3
4	3	0	0	132	3	0	1	260	3	0	2	388	3	0	3
5	4	0	0	133	4	0	1	261	4	0	2	389	4	0	3
6	5	0	0	134	5	0	1	262	5	0	2	390	5	0	3
7	6	0	0	135	6	0	1	263	6	0	2	391	6	0	3
8	7	0	0	136	7	0	1	264	7	0	2	392	7	0	3
9	8	0	0	137	8	0	1	265	8	0	2	393	8	0	3
10	9	0	0	138	9	0	1	266	9	0	2	394	9	0	3
11	10	0	0	139	10	0	1	267	10	0	2	395	10	0	3
12	11	0	0	140	11	0	1	268	11	0	2	396	11	0	3
13	12	0	0	141	12	0	1	269	12	0	2	397	12	0	3
14	13	0	0	142	13	0	1	270	13	0	2	398	13	0	3
15	14	0	0	143	14	0	1	271	14	0	2	399	14	0	3
16	15	0	0	144	15	0	1	272	15	0	2	400	15	0	3
17	16	0	0	145	16	0	1	273	16	0	2	401	16	0	3
18	17	0	0	146	17	0	1	274	17	0	2	402	17	0	3
19	18	0	0	147	18	0	1	275	18	0	2	403	18	0	3
20	19	0	0	148	19	0	1	276	19	0	2	404	19	0	3
21	20	0	0	149	20	0	1	277	20	0	2	405	20	0	3
22	21	0	0	150	21	0	1	278	21	0	2	406	21	0	3
23	22	0	0	151	22	0	1	279	22	0	2	407	22	0	3
24	23	0	0	152	23	0	1	280	23	0	2	408	23	0	3
25	24	0	0	153	24	0	1	281	24	0	2	409	24	0	3
26	25	0	0	154	25	0	1	282	25	0	2	410	25	0	3
27	26	0	0	155	26	0	1	283	26	0	2	411	26	0	3
28	27	0	0	156	27	0	1	284	27	0	2	412	27	0	3
29	28	0	0	157	28	0	1	285	28	0	2	413	28	0	3
30	29	0	0	158	29	0	1	286	29	0	2	414	29	0	3
31	30	0	0	159	30	0	1	287	30	0	2	415	30	0	3
32	31	0	0	160	31	0	1	288	31	0	2	416	31	0	3
33	32	0	0	161	32	0	1	289	32	0	2	417	32	0	3
34	33	0	0	162	33	0	1	290	33	0	2	418	33	0	3
35	34	0	0	163	34	0	1	291	34	0	2	419	34	0	3

PRESET	1-128			PRESET	129-256			PRESET	257-384			PRESET	385-500		
	PROGRAM	MSB	LSB		PROGRAM	MSB	LSB		PROGRAM	MSB	LSB		PROGRAM	MSB	LSB
36	35	0	0	164	35	0	1	292	35	0	2	420	35	0	3
37	36	0	0	165	36	0	1	293	36	0	2	421	36	0	3
38	37	0	0	166	37	0	1	294	37	0	2	422	37	0	3
39	38	0	0	167	38	0	1	295	38	0	2	423	38	0	3
40	39	0	0	168	39	0	1	296	39	0	2	424	39	0	3
41	40	0	0	169	40	0	1	297	40	0	2	425	40	0	3
42	41	0	0	170	41	0	1	298	41	0	2	426	41	0	3
43	42	0	0	171	42	0	1	299	42	0	2	427	42	0	3
44	43	0	0	172	43	0	1	300	43	0	2	428	43	0	3
45	44	0	0	173	44	0	1	301	44	0	2	429	44	0	3
46	45	0	0	174	45	0	1	302	45	0	2	430	45	0	3
47	46	0	0	175	46	0	1	303	46	0	2	431	46	0	3
48	47	0	0	176	47	0	1	304	47	0	2	432	47	0	3
49	48	0	0	177	48	0	1	305	48	0	2	433	48	0	3
50	49	0	0	178	49	0	1	306	49	0	2	434	49	0	3
51	50	0	0	179	50	0	1	307	50	0	2	435	50	0	3
52	51	0	0	180	51	0	1	308	51	0	2	436	51	0	3
53	52	0	0	181	52	0	1	309	52	0	2	437	52	0	3
54	53	0	0	182	53	0	1	310	53	0	2	438	53	0	3
55	54	0	0	183	54	0	1	311	54	0	2	439	54	0	3
56	55	0	0	184	55	0	1	312	55	0	2	440	55	0	3
57	56	0	0	185	56	0	1	313	56	0	2	441	56	0	3
58	57	0	0	186	57	0	1	314	57	0	2	442	57	0	3
59	58	0	0	187	58	0	1	315	58	0	2	443	58	0	3
60	59	0	0	188	59	0	1	316	59	0	2	444	59	0	3
61	60	0	0	189	60	0	1	317	60	0	2	445	60	0	3
62	61	0	0	190	61	0	1	318	61	0	2	446	61	0	3
63	62	0	0	191	62	0	1	319	62	0	2	447	62	0	3
64	63	0	0	192	63	0	1	320	63	0	2	448	63	0	3
65	64	0	0	193	64	0	1	321	64	0	2	449	64	0	3
66	65	0	0	194	65	0	1	322	65	0	2	450	65	0	3
67	66	0	0	195	66	0	1	323	66	0	2	451	66	0	3
68	67	0	0	196	67	0	1	324	67	0	2	452	67	0	3
69	68	0	0	197	68	0	1	325	68	0	2	453	68	0	3
70	69	0	0	198	69	0	1	326	69	0	2	454	69	0	3
71	70	0	0	199	70	0	1	327	70	0	2	455	70	0	3

PRESET	1-128			PRESET	129-256			PRESET	257-384			PRESET	385-500		
	PROGRAM	MSB	LSB		PROGRAM	MSB	LSB		PROGRAM	MSB	LSB		PROGRAM	MSB	LSB
72	71	0	0	200	71	0	1	328	71	0	2	456	71	0	3
73	72	0	0	201	72	0	1	329	72	0	2	457	72	0	3
74	73	0	0	202	73	0	1	330	73	0	2	458	73	0	3
75	74	0	0	203	74	0	1	331	74	0	2	459	74	0	3
76	75	0	0	204	75	0	1	332	75	0	2	460	75	0	3
77	76	0	0	205	76	0	1	333	76	0	2	461	76	0	3
78	77	0	0	206	77	0	1	334	77	0	2	462	77	0	3
79	78	0	0	207	78	0	1	335	78	0	2	463	78	0	3
80	79	0	0	208	79	0	1	336	79	0	2	464	79	0	3
81	80	0	0	209	80	0	1	337	80	0	2	465	80	0	3
82	81	0	0	210	81	0	1	338	81	0	2	466	81	0	3
83	82	0	0	211	82	0	1	339	82	0	2	467	82	0	3
84	83	0	0	212	83	0	1	340	83	0	2	468	83	0	3
85	84	0	0	213	84	0	1	341	84	0	2	469	84	0	3
86	85	0	0	214	85	0	1	342	85	0	2	470	85	0	3
87	86	0	0	215	86	0	1	343	86	0	2	471	86	0	3
88	87	0	0	216	87	0	1	344	87	0	2	472	87	0	3
89	88	0	0	217	88	0	1	345	88	0	2	473	88	0	3
90	89	0	0	218	89	0	1	346	89	0	2	474	89	0	3
91	90	0	0	219	90	0	1	347	90	0	2	475	90	0	3
92	91	0	0	220	91	0	1	348	91	0	2	476	91	0	3
93	92	0	0	221	92	0	1	349	92	0	2	477	92	0	3
94	93	0	0	222	93	0	1	350	93	0	2	478	93	0	3
95	94	0	0	223	94	0	1	351	94	0	2	479	94	0	3
96	95	0	0	224	95	0	1	352	95	0	2	480	95	0	3
97	96	0	0	225	96	0	1	353	96	0	2	481	96	0	3
98	97	0	0	226	97	0	1	354	97	0	2	482	97	0	3
99	98	0	0	227	98	0	1	355	98	0	2	483	98	0	3
100	99	0	0	228	99	0	1	356	99	0	2	484	99	0	3
101	100	0	0	229	100	0	1	357	100	0	2	485	100	0	3
102	101	0	0	230	101	0	1	358	101	0	2	486	101	0	3
103	102	0	0	231	102	0	1	359	102	0	2	487	102	0	3
104	103	0	0	232	103	0	1	360	103	0	2	488	103	0	3
105	104	0	0	233	104	0	1	361	104	0	2	489	104	0	3
106	105	0	0	234	105	0	1	362	105	0	2	490	105	0	3
107	106	0	0	235	106	0	1	363	106	0	2	491	106	0	3

PRESET	1-128			PRESET	129-256			PRESET	257-384			PRESET	385-500		
	PROGRAM	MSB	LSB		PROGRAM	MSB	LSB		PROGRAM	MSB	LSB		PROGRAM	MSB	LSB
108	107	0	0	236	107	0	1	364	107	0	2	492	107	0	3
109	108	0	0	237	108	0	1	365	108	0	2	493	108	0	3
110	109	0	0	238	109	0	1	366	109	0	2	494	109	0	3
111	110	0	0	239	110	0	1	367	110	0	2	495	110	0	3
112	111	0	0	240	111	0	1	368	111	0	2	496	111	0	3
113	112	0	0	241	112	0	1	369	112	0	2	497	112	0	3
114	113	0	0	242	113	0	1	370	113	0	2	498	113	0	3
115	114	0	0	243	114	0	1	371	114	0	2	499	114	0	3
116	115	0	0	244	115	0	1	372	115	0	2	500	115	0	3
117	116	0	0	245	116	0	1	373	116	0	2				
118	117	0	0	246	117	0	1	374	117	0	2				
119	118	0	0	247	118	0	1	375	118	0	2				
120	119	0	0	248	119	0	1	376	119	0	2				
121	120	0	0	249	120	0	1	377	120	0	2				
122	121	0	0	250	121	0	1	378	121	0	2				
123	122	0	0	251	122	0	1	379	122	0	2				
124	123	0	0	252	123	0	1	380	123	0	2				
125	124	0	0	253	124	0	1	381	124	0	2				
126	125	0	0	254	125	0	1	382	125	0	2				
127	126	0	0	255	126	0	1	383	126	0	2				
128	127	0	0	256	127	0	1	384	127	0	2				